

TECHNICAL DATA SHEET

Product code & description:

UDML8002 WESTACURE DUCT MATT FOIL STAMPABLE LITHO OP INK

Application:

UDML8002 WESTACURE DUCT MATT FOIL STAMPABLE LITHO OP INK is specialty product that provides excellent matt effect on print when applied through plate. It can be a contrast coating to give matt and gloss hybrid effect when applied through duct in an offset (Both Dry and Wet offset) on Board or Metpet substrate printed on either UV or Conventional offset Inks. It can be used for spot varnishing through plate.

Key Properties:

- Excellent matt effect
- Good Rub resistance
- Good Over-printability
- Foil Stampable
- Good Ink water Balance
- Stable Emulsification

Substrate:

Recommended for use on coated paper, board and Metpet. When overprinting on highly absorbent substrates it is always advised to check their performance on the actual batch of stocks used before commencing a full production run.

Suitable for use on coated Metallized Polyester (≥ 42 dynes/cm) - preferably primer coated by water-based varnish.

Instructions for Use

- | | |
|------------------------|---|
| • Stir well before use | |
| • Application | Through Wet Offset, Dry Offset or Letterpress |
| • Viscosity | Ready for use |
| • Varnish coat weight | 1.5 — 2.5 gsm (as per requirement) |
| • Cleaning | Immediately with proper solvent |

Curing:

The OP Ink converts into a solid film by radical polymerization initiated by UV radiation in the range of 200 -400 nm. Capacity of the lamp is 80 -120 watts/cm.

Machine Speed

Depends on the Type and age of the lamp.

Technical Characteristics:

Color Appearance:	Thick off-white paste
Viscosity by Falling bar @30°C:	270 ± 10 Poise
Specific gravity:	1 – 1.2
Volatility:	0 %

Product safety:

UV products are generally considered to be non-toxicological. However, during handling and use, avoid inhalation of vapor and direct eyes or skin contact. It can be irritating, wash and rinse immediately with soap & water. Protective eyewear and latex gloves are recommended while using this product. Refer MSDS for additional handling and safety information.

Shelf life:

UDML8002 is stable for 6 months when stored in its original container at temperatures between 5°C and 25°C, away from direct sunlight. Contaminated material should not be returned to the original container or re-used.

Cleaning:

Clean the plates, rubber roller, steel roller, anilox roll and other equipment with recommended cleaning agent, after use.

Packaging:

This product is available in 1 or 2 Kg plastic pail.

NOT SUITABLE FOR DIRECT CONTACT FOOD PACKAGING

Disclaimer:

This information is furnished without warranty, expressed, or implied, except that it is accurate to the best knowledge of Westtek Enterprises Private Limited. The data on the sheet is related to specific product designated herein. Westtek Enterprises Private Limited assumes no legal responsibility for use or reliance upon these data.

Issued Date: Apr 2023- Version: V1.0
